
http://www.peaklift.cn

# MODEL 409 Non-Alignment Four-post Lift





EXCLUSIVE FEATURE !

Electric control device With UP, LOCK and DOWN buttons

With C.E. stop switch at 300 mm from ground and alarm tone when lowering down from 300 mm to ground make the lift more safety.



Oil-water separator and Solenoid air valve are installed on the power side column.



**Optional Air Line Kits** All peak four post lifts are designed to use the air line kits for rolling jack.

Kits No.:40102

### Optional Rolling Jacks J6H: manual hydraulic type 2.8 T J6A: pneumatic hydraulic type 2.8 T


RJ - 8A: pneumatic hydraulic type 3.5 T


#### SPECIFICATIONS

Model	Lifting Capacity	Lifting Time	А	В	С	D	Е	F	G	Н	I	J	K	Gross Weight	Motor Power
				Overall Length (No Inc.Ramps)		Width Between Posts	Max. Lifting Height	Overall Height	Minmum Height		Drive-Thru Clearance	Width Between Runways	Outside Edge of Runways		
409	4.0T (9,000lbs)	45S	5512mm (217")	4600mm (181 1/8")	3208mm (126 1/4")				170mm (6 3/4")	1724mm (67 7/8")	2498mm (98 3/8")	1100mm(43 1/4") Max.1300mm (51 1/8")	2116mm(83 1/4") Max.2316mm (91 1/8")	917kg (2,021lbs)	3.0HP


## FEATURES

- Electric-air control operation system.
- Mechanical self-lock and air-drived safety release.
- Electrical hydraulic power system, cable-drived.
- Non-skid diamond platform.
- Adjustable lifting platform: Off-side platform can be adjusts the mounting position left or right as required. The standard distance between two platforms is 1100mm and maximum distance is 1300mm.
- Dual safety device: In case the primary safety locks are out of operation, the lift would also be locked automatically by a second safety device.
- Optional Jack.










Double-safety locks.



The 4-post LED Light kits is fitted for every model of PEAK 4-post lifts . Kits No.:40104



Optional platform extension kits add an extra 660mm(26") length to the platform. Kits No.:40903



Optional adjustable blocks for alignment 4 post lift. Kits No.:40905 (used with kits 40903 or 41203)